

DESKTOP AUTOMATIC DIAMOND SETTING MACHINE

ONE MACHINE DO 10 WORKERS' JOB











- Advantages -




2ND EQUIPMENT INTRODUCTION.




Suitable for wax setting on flat, curved, and three-dimensional surfaces.lt supports wax setting for diamonds sized 0.8-3.0, such as zircon, moissanite, rhine.stone, etc.





3RD APPLICATION SCENARIO







4TH BASIC OPERATION

Step-1→Flip the switch

Step-2→Prepare the diamonds

Step-3→Place the mold

Step-4→Adjust the points

Step-5→Click to start

5TH PRODUCTS SERVICE



Common Problems Found and Solve...



Equipment Advanced Instructional Vi...



Machine maintenance instruction.rar

Mozzle introduction and disassembly...

Positioning mold making instruction.r...

Teaching by demonstration.rar

Online Teaching Videos



Offline Teaching

6TH SHIPMENT PROCESS



 ${\sf Sensing} {\rightarrow} {\sf Cleanse} {\rightarrow} {\sf Pack} {\rightarrow} {\sf Crating} {\rightarrow} {\sf Shipment}$



Equipment Name	Mini Wax Setting Machine
Equipment Model	SPB-ASM1
Workbench Structure	Five-axis linkage workbench
Running Speed	9,000-12,000 diamonds per hour
Number of Suction Drill Bits	3 suction nozzles
Drill Plate Fixing Method	Movable spring top screw on the upper side of the platform
Drilling Accuracy	±0.02mm
Control System	Industrial-grade five-axis motion controller
Drive System	High-end servo
Transmission Method	High-precision screw guide
XYZ/A/C Effective Stroke	200° 95*150mm/+159° -5° /±360°
Working Air Pressure	80psi (0.4Mpa)
Equipment Appearance Size	Length 710 * width 600 * height 670mm
Equipment Weight	About 116KG

Superb Electromachinery Co., Limited

- Add:No.55 Anhua Road, Anliang Village, Henggang Town Longgang District, Shenzhen City, China.
- & Tel:0086-755-28838424
- Fax:0086-755-28883730
- © Whatsapp:+8618857719978